


Robolino 3000

Art. Nr. 119 356




E 119356 1/4

| | | | | | |
|---|---|---|---|---|---|
| a | b | c | d | e | f |
| * | * | * | * | * | * |

Robolino 3000

Art. Nr. 119 356




E 119356 2/4

| | | | | | |
|---|---|---|---|---|---|
| a | b | c | d | e | f |
| * | * | * | * | * | * |

Robolino 3000

Art. Nr. 119 356

AL-KO




E 119356 3/4

| | | | | | |
|---|---|---|---|---|---|
| a | b | c | d | e | f |
| * | * | * | * | * | * |

Robolino 3000 Basisstation

Art. Nr. 470 884



E 119356 4/4

| | | | | | |
|---|---|---|---|---|---|
| a | b | c | d | e | f |
| * | * | * | * | * | * |